

NPC-D-5200 Series

Digital Controllers





A standalone single axis closed loop piezo actuator controller designed to cover a wide range of challenging applications needing the best dynamic performance. There is no compromise; the NPC-D-5200 delivers precision, accuracy and speed.

Key Features

- Precision capacitive sensor measurement circuit for closed loop operation.
- Update rate of 8.3 micro seconds (120KHz)
- Low electronic noise. The low noise design allows stage position noise as low as a few tens of picometres.
- High power rating, -30 to +150V drive with 160mA continuous current as standard.
- Stage designs incorporate capacitive sensors which give precise positional feedback in closed loop mode delivering high resolution/low noise and high linearity of movement.
- The controller is updated with the position of the stage 120000 times per second. This contributes to high speed positioning accuracy for applications that need high speed movement of the stage.
- A stable system which delivers repeatability of movement with improved precision and accuracy for precise imaging & focusing.
- The high power rating allows stages to be driven at higher maximum speeds with faster step settle times.
 This can be particularly important for longer range stages or stages designed for high load bearing.



NPC-D-5200 Series

Digital Controllers

Interfacing

- Analogue command and position output +/-10 V
- Digital commands over USB or optional RS232C and Ethernet control interfaces.
- Easy to interface with OEM software using supplied DLL (Dynamic Link Library). In position digital outputs can be used to interface with external devices. Expansion slot to allow custom board for OEM integration.
- Examples of software in C/C++, Python and LabVIEW® provided.
- · User programmable Function Playback of custom programmed waveforms such as constant velocity profiles.
- TTL input/output triggers f or external control.Programmable when "Function playback" feature used.
- TTL In-Position output to indicate when NanoMechanism reaches the desired/set position (user selectable position accuracy).

Technical specification

Parameter	Value	Units	Comments		
Mechanical	,	'			
Size (Width x Depth x Height) Height includes feet Not including protruding components at front and rear of controller	268 x 194 x 70	mm	Additional space required for rear connectors and cables.		
Weight	1.7	kg			
Cooling	Fan forced air		Vents on rear and base		
Electrical	Electrical				
Power input	96 to 265 47 to 63	Vrms Hz	Using external supply. Only use approved power supply provides protective earth connection.		
DC power input	± 24 ± 0.75@5A	V	Only use Queensgate approved power supply		
DC power input connector	4 pin DIN Plus protective earth connection		Rear panel		
Connectivity	Connectivity				
USB	2.0 compliant		USB type B connector. Note: power not taken from USB port.		
Ethernet	IEEE 802.3		RJ45 connector. Requires a Cat 5 male to male cable. MUST use shielded Ethernet cable.		
Analogue input command	BNC		Per channel - front panel		
Analogue Position Monitor output	BNC		Per channel - front panel		
"TRIG" input, "TRIG" output, "IN-POS" output and Quadrature Interface	25 pin D-type socket				
Controller Synchronizing signals	9 pin D-type socket		Rear panel		
Environmental - Operational					
Temperature	10 to 40	°C			
Relative Humidity	5 to 80	%RH	Non-condensing		
Environmental - Storage and Shipping					
Temperature	-20 to 70	°C			
Relative Humidity	0 to 95	%RH	Non-condensing		



NPC-D-5000 Series
Closed Loop Digital Controllers

Technical specification

Parameter	Value	Units	Comments	
General	'	'		
Warm up time	40 (typ)	Min		
"ANA I/P" analogue input position command per channel	-10 to +10	V	Connector BNC – Single ended MAXIMUM input: ±15V	
"ANA I/P" analogue input impedance (per channel)	> 50k	Ohms		
"POS MON" analogue output position monitor per channel	-10 to +10		Connector BNC – Single ended MAXIMUM input: ±15.5V	
"IN- POSITION" Output	Logic "0" < 0.8 Logic "1" 2.4 to 5	V	15 pin D-Type on rear panel. For OUTPUTS Load impedance: > 1k ohms. MAXIMUM	
"TRIG"	Logic "0" < 0.8 Logic "1" 2.4 to 5	V V	output: 5.5V For INPUTS Input impedance: 50 ohms. MAXIMUM input: 5.5V	
NanoMechanism interfacing – controller – per channel				
Connector	17W2 D type		Mixed signal connector	
HV output swing	-30 to +150 -20 to +120	V	Factory set (default) Factory set (optional)	
HV drive current	160	mA	Factory set (default)	
HV amplifier bandwidth	>50	kHz		
HV amplifier intrinsic noise	0.3	mV		
"ANA I/P" analogue output position command	-5 to +5	V	Connector BNC Differential input - core +ve	
"POS MON" analogue output position monitor	-5 to +5	V	Connector BNC Single ended	
"READY" output signal	Logic "0" <0.8 Logic "1" 2.4 to 5	V V	Connector BNC	
"TRIG I/P" input signal	Logic "0" <0.8	V		

Ordering information

Product Ref	Description
QGNPC-D-5200	NPC-D-5200 Single axis high performance digital controller.

Owing to continuous development, we reserve the right to introduce improvements and modify specifications without prior notice.



WORLDWIDE DISTRIBUTION



Prior Scientific Ltd Cambridge, UK

t: +44 (0)1223 881711 e: uksales@prior.com



Prior Scientific Inc Rockland MA U.S.A

t: +1 781-878-8442 e: info@prior.com



Prior Scientific GmbH Jena, Germany

t: +49 (0) 3641 675 650 **e:** jena@prior.com



Prior Scientific KK Tokyo, Japan

t: +81-3-5652-8831 e: info-japan@prior.com



Prior Scientific China Suzhou, China

t: +86 (0)512 6617 5866 e: info-china@prior.com

